


SmallRig



LA-O65 Octagonal Softbox

LA-O65 快拆八角柔光箱

Operating Instruction / 操作指引

- Thank you for purchasing SmallRig's product.
- Please read this Operation Guide carefully.
- Please follow the safety warnings.
- The child can only operate this device with the guidance of adults, please do not let them operate this device alone.
- 感谢您购买 SmallRig 产品。
- 使用本产品之前，请仔细阅读操作指引。
- 请注意所有警告提示并遵循使用操作指引的所有指令。
- 儿童只能在成年人的指导下操作本设备，请不要让他们单独操作。

SmallRig LA-O65 Octagonal Softbox is versatile soft light accessory with a 65cm diameter.

Universal Bowens Mount design, makes it compatible with SmallRig RC 120D / RC 120B / RC 220D / RC 220B / RC 350D / RC 350B / RC 450D / RC 450B and other Bowens Mount Light of other brands.

The quick release design, the diffusion and the frame are combined into one, you can easily assemble and disassemble the dome in a few seconds, simplifying the use process, bringing you the best user experience.

LA-O90 also includes a high-quality fabric grid to help you focus the light beam angle to 45 degrees, which will allow you to maximize control of your lighting.

The Octagonal Softbox adopts industrial-grade soft material and highly reflective coating with two diffusions for a stronger soft effect or higher light transmission to satisfy your different needs.

SmallRig LA-O65 快拆八角柔光箱是一款直径为65cm多用八角柔光箱。

接口形式为通用的保荣口设计，除了兼容 SmallRig RC 120D / RC 120B / RC 220D / RC 220B / RC 350D / RC 350B / RC 450D / RC 450B 外，同时还兼容市面上其他品牌保荣卡口的点光源。

采用最新一代快拆结构，一键可完成装卸，简化使用流程，带给您最好的用户体验。

标配 45°格栅，有效约束光线范围，适用更多场景。

采用工业级柔光材料和高反光涂层，并标配两块柔光布，获得更强的柔光效果或者更高的光通过性，满足您的不同需求。

In the Box 包装清单

Octagonal Softbox 八角柔光箱	× 1	Honeycomb Grid 格栅	× 1
Diffusion Fabric (Internal) 内柔光布	× 1	Carrying Bag 收纳包	× 1
Diffusion Fabric (External) 外柔光布	× 1	Operating Instruction 操作指引	× 1

Installation & Removal 安装 / 拆卸



1. Pull the gray hand grip on the mounting plate, Installation is complete upon a "click" sound.

1. 用力将灰色握手位扣到卡盘上，听到咔声后安装完成。



2. Attach the internal diffusion to the softbox with velcro.

2. 依次将内柔光布粘贴到柔光箱上的魔术贴扣上。



3. Attach the external diffusion to the edge of the softbox with velcro.

3. 然后将外柔光布沿着柔光箱内侧边缘粘贴到黑色魔术贴上。



4. Attach the honeycomb grid to the edge of the softbox with velcro.

4. 最后将格栅粘贴到柔光箱外边缘黑色魔术贴上。



5. Disassembly: Pinch release button, until the "click" sound to disassemble.

5. 拆卸：对捏解锁按键，听到“咔”声后完成拆卸。

Specifications

产品参数

Product Name 产品名称	LA-O65 Octagonal Softbox LA-O65 快拆八角柔光箱
Opening Softbox Size 柔光箱展开尺寸	Φ650.0 x 380.0mm (±20.0 - 30.0mm)
Diffusion Fabric (Internal) Size 内柔光布尺寸	Φ490.0mm (±20 - 30mm)
Diffusion Fabric (External) Size 外柔光布尺寸	Φ620.0mm (±20.0 - 30.0mm)
Honeycomb Grid Size 格栅尺寸	Φ610.0mm (±20.0 - 30.0mm)
Product Weight 产品净重	840.0g / 1.85lbs

Specifications subject to change without prior notice. Please refer to the physical product for the most up-to-date information. / 技术参数如有改动，以实物为准，恕不另行通知。

Service & Warranty

Please keep your original receipt and guarantee card. Be sure the dealer has written on it the date of purchase and SN of the product. These are required for warranty service.

After-sale Warranty Terms

SmallRig products are entitled to warranty services as of the date of payment.

- Electronic products (except V mount battery): 1-year warranty.
- V mount battery: 2-year warranty.
- Non-electronic products: 2-year warranty.

Note: In case of any conflict between our warranty period policy and applicable laws and regulations of the country / region where the products are sold, the latter shall prevail.

This Warranty Does Not Cover

1. If users fail to adhere to the "Operating Instruction" or any "Warnings" stated in the user manual, resulting in a quality failure, it falls outside the scope of warranty coverage.
2. The product identification or SN label is removed or defaced in any way.
3. Product damage caused by problems not attributable to the quality of the products such as improper use of the products.
4. Product damage caused by unauthorized modification, disassembly, repair and other acts.
5. Product damage caused by fires, floods, lightning and other force majeure factors.

Warranty Mode

- For the products within the scope of warranty, SmallRig will repair or replace them on the basis of specific failures; the repaired / replaced products / parts are entitled to the remaining part of the original warranty period.

Contact Information

- You're advised to contact the online customer service personnel of corresponding shopping platform and submit a repair service application.
- You may also apply for repair service through SmallRig's service email.

Service Email: support@smallrig.com

保修条款

请保留您的原始购买单据及保修卡,同时包含您的购买日期、产品序列号等,这些资料质保服务时均需要提供。

售后质保条款

SmallRig产品自下单付款之日起享有质保服务。

- 电子产品(除V口电池): 1年质保。
- V口电池: 2年质保。
- 非电子产品: 2年质保。

注:若销售地国家或地区的适用法律法规有冲突的,以销售地国家或地区有关质保期的法律法规为准。

质保无效说明

1. 当用户违反操作指引或用户手册中“重要提示”任何一条导致的质量失效,不在质保范围内。
2. 产品序列号标识已经被撕毁或无法辨识,不在质保范围。
3. 产品使用不当等非产品本身质量问题,而造成的产品损坏,不在质保范围。
4. 非官方指导的私自改装、拆解、维修等行为而造成的损坏,不在质保范围。
5. 因火灾、水灾、雷击等不可抗力造成的产品损坏,不在质保范围。

维修方式

·属于质保范围的,SmallRig 根据产品具体的故障对产品进行维修或更换;维修后的产品 / 部件享受原有保修期的剩余时长。

联系方式

- 建议您优先前往相应购买平台联系在线客服,提出产品维修申请。
- 您也可以通过 SmallRig 服务邮箱申请维修服务。

服务邮箱:support@smallrig.com

Guarantee Card / 保修卡

ID No. ID 编号	
Item Name 产品名称	
Purchase Date 购买日期	
User Name 用户姓名	
Mobile 用户电话	
Address 用户地址	
Receipt 购买单据	

执行标准: GB/T 26572-2011

Manufacturer: Shenzhen Leqi Innovation Co., Ltd.

制造商: 深圳市乐其创新股份有限公司

Add: Rooms 103, 501 and 601, Building 5, Fenghe Industrial Park, Nos. 1301-50 Guanguang Road,
Longhua District, Shenzhen, Guangdong, China.

地址: 中国广东省深圳市龙华区观澜街道新澜社区观光路1301-50号丰和工业园厂房5栋103、501、601

Consignor: Shenzhen LC Co., Ltd.

委托商: 深圳市乐长科技有限公司

Add: Rooms 602, Building 5, Fenghe Industrial Park, No. 1301-50 Guanguang Road, Xinlan Community,
Guanlan Street, Longhua District, Shenzhen, Guangdong, China.

地址: 中国广东省深圳市龙华区观澜街道新澜社区观光路1301-50号丰和工业园厂房5栋602

EC	REP	Prolinx GmbH Brehmstr.56,40239 Duesseldorf Germany eu@eulinx.eu
----	-----	---

UK	REP	Prolinx Global LTD 27 Old Gloucester Street London, WC1N3AX, UK eu@eulinx.eu
----	-----	--

CE RoHS



LQ-B386-18

WE ARE HERE FOR YOU
服务与支持

ETICHETTATURA AMBIENTALE
ENVIRONMENTAL LABELING