

SmallRig



Right-Angle 15mm Rod Clamp

Operating Instruction

SmallRig 90 Degree 15mm Rod Clamp 2069 are used to attach 15mm rods for different shooting scenarios. It could be locked tight via 2 wingnuts. It could attach 15mm rod and then 15mm Micro Rod(1.5") with 1/4" Thread 1552 for monitor. It features quick attachment and release during this process. It could attach 15mm rod of dual-rod system for run-and-gun operation. It could be mounted on 15mm Rod with 1/4 Inch Screw Hole 1182 for magic arm whereby monitor could be attached. It could attach 15mm rod and then Microphone Shock for microphone.

Safety Guidelines

1. Environment

Do not use the product underwater, in extreme temperatures (e.g., freezing or direct heat), corrosive environments, or excessive dust. Dry metal parts immediately after liquid contact to prevent corrosion.

2. Load Capacity

Do not exceed the maximum weight capacity indicated on the product. Overloading risks structural failure, deformation, or accidental drops.

3. Cleaning & Maintenance

Clean surfaces with a dry, soft cloth. Avoid chemicals like alcohol or solvents. Ensure dry and ventilated conditions for long-term storage.

4. Structural Integrity

Do not modify the product (e.g., drilling, cutting)—this compromises structural integrity and increases drop risks.

5. Malfunctions

Stop use immediately if you notice deformation, unusual noises, or loose components, and contact support.


In the Box

90 Degree 15mm Rod Clamp × 1

Guarantee Card × 1

Product Details





Specifications



Product Dimensions: 68.5 x 26.5 x 26.5mm

Net Weight: 46g

Package Size: 85 x 75 x 24mm

Material: Aluminum Alloy

Manufacturer Email: support@smallrig.com

Manufacturer: Shenzhen Leqi Innovation Co., Ltd.

Add: Rooms 101, 701, 901, Building 4, Gonglianfuji Innovation Park, No. 58, Ping'an Road, Dafu Community, Guanlan Street, Longhua District, Shenzhen, Guangdong, China.

Consignor: Shenzhen LC Co., Ltd.

Add: Room 201, Building 4, Gonglianfuji Innovation Park, No. 58, Ping'an Road, Dafu Community, Guanlan Street, Longhua District, Shenzhen, Guangdong, China.

RoHS

CE



Séparez les éléments avant de trier



Made in China