


SmallRig



LA-090 Octagonal Softbox

LA-090 快拆八角柔光箱

Operating Instruction / 操作指引

- Thank you for purchasing SmallRig's product.
 - Please read this Operation Guide carefully.
 - Please follow the safety warnings.
 - The child can only operate this device with the guidance of adults, please do not let them operate this device alone.
-
- 感谢您购买 SmallRig 产品。
 - 使用本产品之前, 请仔细阅读操作指引。
 - 请注意所有警告提示并遵循使用操作指引的所有指令。
 - 儿童只能在成年人的指导下操作本设备, 请不要让他们单独操作。

Thank you for purchasing SmallRig LA-O90 Octagonal Softbox.

感谢您购买 SmallRig LA-O90 快拆八角柔光箱。

SmallRig LA-O90 Octagonal Softbox is a kind of versatile soft light accessory with 90cm diameter.

SmallRig LA-O90 快拆八角柔光箱是一款直径为90cm多用八角柔光箱。

Universal Bowens Mount design, makes it compatible with SmallRig RC 120D / RC 120B / RC 220D / RC 220B / RC 350D / RC 350B / RC 450D / RC 450B and other Bowens Mount Light of other brands.

接口形式为通用的保荣口设计, 除了兼容 SmallRig RC 120D / RC 120B / RC 220D / RC 220B / RC 350D / RC 350B / RC 450D / RC 450B 外, 同时还兼容市面上其他品牌保荣卡口的点光源。

The quick release design, the diffusion and the frame are combined into one, you can easily assemble and disassemble the dome in a few of seconds, simplifying the use process, bringing you the best user experience.

采用最新一代快拆结构, 一键可完成装卸, 简化使用流程, 带给您最好的用户体验。

LA-O90 also include a high-quality fabric grid to help focus in your light beam angle to 45 degrees, which will allow you to maximize control of your lighting.

标配 45°格栅，有效约束光线范围，适用更多场景。

The Octagonal Softbox adopt industrial-grade soft material and highly reflective coating with two diffusions for a stronger soft effect or higher light transmission to satisfy your different needs.

采用工业级柔光材料和高反光涂层，并标配两块柔光布，获得更强的柔光效果或者更高的光通过性，满足您的不同需求。

In the Box

包装清单

Octagonal Softbox 八角柔光箱	× 1	Carrying Bag 收纳包	× 1
Honeycomb Grid 格栅	× 1	Operating Instruction 操作指引	× 1
Internal Diffusion 柔光布 (内)	× 1	Guarantee Card 保修卡	× 1
External Diffusion 柔光布 (外)	× 1		

Installation & Removal

安装 / 拆卸



1. Pull the gray hand grip on the mounting plate, Installation is complete upon a “click” sound.

1. 用力将灰色握手位扣到卡盘上，听到咔声后安装完成。



2. Attach the internal diffuser to the softbox with velcro.

2. 依次将内柔光布粘贴到柔光箱上的魔术贴扣上。



3. Attach the external diffuser to the edge of the softbox with velcro.

3. 然后将外柔光布沿着柔光箱内侧边缘粘贴到黑色魔术贴上。



4. Attach the honeycomb grid to the edge of the softbox with velcro.

4. 最后将格栅粘贴到柔光箱外边缘黑色魔术贴上。



5. Disassembly: Pinch release button, until the “click” sound to disassemble.

5. 拆卸：对捏解锁按键，听到“咔”声后完成拆卸。

If there are any change to the technical specifictions, the ectual product shall prevail, without furter notice.

技术参数如有改动，以实物为准，恕不另行通知。

Specifications

产品参数

Product Name 产品名称	LA-O90 Octagonal Softbox LA-O90 快拆八角柔光箱
Opening Softbox Size 柔光箱展开尺寸	φ900mm × 450mm / 34.6in × 17.7in
External Diffuser Size 柔光布尺寸(外)	Φ830mm / 32.7in
Internal Diffuser Size 柔光布尺寸(内)	Φ600mm / 23.6in
Honeycomb Grid Size 格栅尺寸	Φ830mm / 32.7in
Product Weight 产品净重	900g / 1.98lbs

Manufacturer Email: support@smallrig.com

Manufacturer: Shenzhen Leqi Innovation Co., Ltd.

制造商: 深圳市乐其创新股份有限公司

Add: Rooms 101, 701, 901, Building 4, Gonglianfuji Innovation Park, No. 58, Ping'an Road,

Dafu Community, Guanlan Street, Longhua District, Shenzhen, Guangdong, China.

地址: 中国广东省深圳市龙华区观澜街道大富社区平安路58号共联富基创新园4栋101、701、901

Consignor: Shenzhen LC Co., Ltd.

委托商: 深圳市乐长科技有限公司

Add: Room 201, Building 4, Gonglianfuji Innovation Park, No. 58, Ping'an Road,

Dafu Community, Guanlan Street, Longhua District, Shenzhen, Guangdong, China.

地址: 中国广东省深圳市龙华区观澜街道大富社区平安路58号共联富基创新园4栋201



Séparez les éléments avant de trier



执行标准: GB/T 26572-2011

LQ-B258-18